




## Washing machine Type 160

Cleans cylindrical screens and hollow blades with solvent. Very good cleaning results due to rotation of the cylindrical screens and hollow blades and due to short spraying distances combined with a powerful washing pump. The solvent tank is separated from the washing chamber; hence emissions are considerably reduced. The machine can be adapted to various tasks with the appropriate accessories. The washing machine is type-examined and explosion-proof (category 1/2) in accordance with ATEX.



### Dimension:

**W-160RS1** (1 long rotary screen, 1 doctor blade)

**Wama 160RS1-10**

max. length of rotary screen:	1000 mm
max. length of doctor blade:	1700 mm

**Wama 160RS1-15**

max. length of rotary screen:	1500 mm
max. length of doctor blade:	2300 mm


**W-160RS2** (2 long rotary screens, 2 doctor blades)

**Wama 160RS2-10**

max. length of rotary screen:	1000 mm
max. length of doctor blade:	1700 mm

**Wama 160RS2-15**

max. length of rotary screen:	1500 mm
max. length of doctor blade:	2300 mm



### Items to be washed



### cleaning process



### cleaning agents

