

RENZMANN

Washing machine for mixing vessels

6090

Cleaning with solvent



For cylindrical vessels with/ without outlet

EXCELLENT CLEANING



- Clean containers = less downtime

EASY HANDLING



- Short and reliable washing cycles

HIGH-QUALITY



- High-end components and sturdy construction

TECHNICAL DATA

Vessel Ø [mm]

Vessel height [mm]

Internal Air Extraction [m³/h]

Dimensions D x W x H [mm]

STANDARD SIZE

350 – 600

200 – 900

2200

2050 x 1400 x 1850

Technical changes reserved



Sustainability First!
Combine washing and
distilling




Why a 6090?



EFFICIENT CLEANING:

Efficient internal and external cleaning of barrels and small cylindrical containers with brushes. Washing with recirculating washing solvent and rinsing with clean solvent.



EASY HANDLING:

Automatic washing program and washing chamber tilted backwards for optimal drainage and prevention of residue.



SAFE USE:


Conductive brushes with type examination. Explosion protection according to ATEX, category 1 (with type examination) for zone 0 inside, category 2 for zone 1 outside the machine.



ROBUST DESIGN:

High-quality components like pumps and ventilators. Long life cycle with regular maintenance.

Before/ After



Partner with our **multidisciplinary experts** for **tailored advice** and **worldwide customer care!**

Washing/Distillation Trials
technikum@dw-renzmann.de

Consultation
vertrieb@dw-renzmann.de

Service and Maintenance
service@dw-renzmann.de